



Kabel koneksi dengan soket

ADOAF030MSS07,5E03

Produk tidak tersedia - entri arsip



Data kelistrikan

Tegangan pengoperasian	[M]	< 60 AC / < 75 DC
Kelas perlindungan		III

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67

Data teknis

Dimensi	[mm]	17 x 10 x 26
Material		TPU
Material bodi detakan		TPU
Material mur		kuningan, berlapis nikel

Keterangan

Jumlah paket		1 buah
--------------	--	--------

Koneksi listrik

Kabel: 7.5 m, PVC, oranye, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Koneksi listrik - soket

Konektor: 1 x M8, bersiku; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel
Konektor: 1 x M8, bersiku; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



E10538



Kabel koneksi dengan soket

ADOAF030MSS07,5E03

Koneksi



BK =	Warna core :
BN =	hitam
BU =	coklat
	biru