

E10590



Kabel koneksi dengan soket

ADOAH042VAS0005E03

Produk tidak tersedia - entri arsip



Data kelistrikan		
Tegangan pengoperasian	[V]	10...30 DC
Output		
Desain kelistrikan		PNP
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67
Data teknis		
Material		PUR
Material bodi detakan		PUR
Material mur		baja tahan karat (1.4305/303)
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 5 m, PVC, hitam, Ø 4.5 mm; 3 x 0.34 mm ² (182 x Ø 0.05 mm)		
Koneksi listrik - soket		
Konektor: 1 x M12, bersiku; pengkodean: A; Bodi cetakan: PUR; Penguncian: baja tahan karat (1.4305/303)		

E10590



Kabel koneksi dengan soket

ADOAH042VAS0005E03

Koneksi



BK =
BN =
BU =

Warna core :
hitam
coklat
biru