




Kabel koneksi

VDOGF030MSS00,8A03STGF030MSS

Produk tidak tersedia - entri arsip



Data kelistrikan		
Tegangan pengoperasian	[V]	< 60 AC/DC
Kelas perlindungan		III

Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...90
Perlindungan		IP 68

Data teknis		
Material		PUR
Material bodi detakan		PUR
Material mur		seng tuang, berlapis nikel

Keterangan		
Jumlah paket		1 buah

Koneksi listrik - colokan

Konektor: 1 x M8, lurus; pengkodean: A; Bodi cetakan: PUR; Penguncian: seng tuang, berlapis nikel



E10605




Kabel koneksi

VDOGF030MSS00,8A03STGF030MSS

Koneksi listrik

Kabel: 0.8 m, PUR / PVC; 3 x 0.25 mm² (128 x Ø 0.05 mm)

Koneksi



Koneksi listrik - soket

Konektor: 1 x M8, lurus; pengkodean: A; Bodi cetakan: PUR; Penguncian: seng tuang, berlapis nikel

