

E10610



Kabel koneksi dengan soket

ADOAH042VAS0010E03

Produk tidak tersedia - entri arsip



Data kelistrikan	
Tegangan pengoperasian	[V] 10...30 DC
Output	
Desain kelistrikan	PNP
Kondisi pengoperasian	
Suhu sekitar	[°C] -25...90
Perlindungan	IP 67
Data teknis	
Material	PUR
Material bodi detakan	PUR
Material mur	baja tahan karat (1.4305/303)
Keterangan	
Jumlah paket	1 buah
Koneksi listrik	
Kabel: 10 m, PVC, hitam, Ø 4.5 mm; 3 x 0.34 mm²	
Koneksi listrik - soket	
Konektor: 1 x M12, bersiku; pengkodean: A; Bodi cetakan: PUR; Penguncian: baja tahan karat (1.4305/303)	

E10610



Kabel koneksi dengan soket

ADOAH042VAS0010E03

Koneksi



BK =
BN =
BU =

Warna core :
hitam
coklat
biru