




Kabel koneksi dengan colokan

ASTGH030MSS0002A03

Produk tidak tersedia - entri arsip



Data kelistrikan		
Tegangan pengoperasian	[V]	10...55 DC
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67
Data teknis		
Dimensi	[mm]	15 x 15 x 42
Material		TPU
Material bodi detakan		TPU
Material mur		kuningan, berlapis nikel
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 2 m, PUR / PVC, oranye, Ø 4.9 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)		
Koneksi listrik - colokan		

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



E10665



Kabel koneksi dengan colokan

ASTGH030MSS0002A03

Koneksi

1	BN
3	BU
4	BK

	Warna core :
BK =	hitam
BN =	coklat
BU =	biru