

E10951



Kabel koneksi

VDOGH040MSS0002H04STGH040MSS

Produk tidak tersedia - entri arsip



Aplikasi

Fitur khusus	Bebas halogen
--------------	---------------

Data kelistrikan

Tegangan pengoperasian	[V]	< 250 AC / < 300 DC
------------------------	-----	---------------------

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67

Data teknis

Dimensi	[mm]	15 x 15 x 42
Material		TPU
Material bodi detakan		TPU
Material mur		kuningan, berlapis nikel

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik - colokan

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



Kabel koneksi

VDOGH040MSS0002H04STGH040MSS

Koneksi listrik

Kabel: 2 m, PUR, Bebas halogen; 4 x 0.34 mm²

Koneksi



Koneksi listrik - soket

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel

