




Kabel koneksi dengan soket

ADOAG030--S0005A03

Produk tidak tersedia - entri arsip



Data kelistrikan		
Tegangan pengoperasian	[V]	< 60 AC/DC
Kelas perlindungan		III


Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67

Data teknis		
Dimensi	[mm]	17 x 8 x 25
Material		PUR
Material bodi detakan		PUR

Keterangan		
Jumlah paket		1 buah

Koneksi listrik		
Kabel: 5 m, PUR / PVC, hitam, Ø 4.5 mm; 3 x 0.25 mm² (128 x Ø 0.05 mm)		

Koneksi listrik - soket		
Konektor: 1 x M8, bersiku; pengkodean: A; Bodi cetakan: PUR; Penguncian: snap-in		






Kabel koneksi dengan soket

ADOAG030--S0005A03

Koneksi



BN =	Warna core :	coklat
BK =		hitam
BU =		biru