

Kabel koneksi dengan soket

ADOGH080MSS0002H08

Untuk soket 8 terminal, warna core tidak distandarisasi.
Perhatikan perkabelan sensor dan soket (lihat lembar data).



Data kelistrikan

Tegangan pengoperasian	[V]	< 30 AC / < 36 DC
------------------------	-----	-------------------

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...80
Perlindungan		IP 68

Data teknis

Berat	[g]	135.9
Dimensi	[mm]	15 x 15 x 43
Material		PUR
Material bodi detakan		PUR
Material mur		kuningan, berlapis nikel

Keterangan

Jumlah paket		1 buah
--------------	--	--------

E11950



Kabel koneksi dengan soket

ADOGH080MSS0002H08

Koneksi listrik

Kabel: 2 m, PUR, hitam, Ø 6.2 mm; 8 x 0.25 mm²

Koneksi listrik - soket

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: PUR; Penguncian: kuningan, berlapis nikel; Torsi pengencangan: 0.7...0.9 Nm



Koneksi

1	BN
2	WH
3	BU
4	BK
5	GY
6	PK
7	VT
8	OG

warna sesuai DIN
EN 60947-5-2

Warna core :

BK =	hitam
BN =	coklat
BU =	biru
GY =	abu-abu
PK =	merah muda
OG =	oranye
VT =	ungu
WH =	putih