

E12432



Kabel koneksi

VDOGH080MSS00,3H03STGH030MSS



Aplikasi

Fitur khusus

Bebas halogen

Data kelistrikan

Tegangan pengoperasian

[V]

< 30 AC / < 36 DC

Kondisi pengoperasian

Suhu sekitar

[°C]

-25...80

Perlindungan

IP 68

Data teknis

Berat

[g]

51

Material

PUR

Material bodi detakan

PUR

Material mur

kuningan, berlapis nikel

Keterangan

Jumlah paket

1 buah

Kabel koneksi

VDOGH080MSS00,3H03STGH030MSS

Koneksi listrik - colokan

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: PUR; Penguncian: kuningan, berlapis nikel; Torsi pengencangan: 0.7...0.9 Nm

**Koneksi listrik**

Kabel: 0.3 m, PUR, Bebas halogen, hitam, Ø 6.8 mm; 3 x 0.25 mm²

Koneksi**Koneksi listrik - soket**

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: PUR; Penguncian: kuningan, berlapis nikel; Torsi pengencangan: 0.7...0.9 Nm

