

Soket adaptor

RSTGA030ALS00.3-03

No scale drawing available

Aplikasi

Fitur khusus

Kontak berlapis emas

Data kelistrikan

Tegangan pengoperasian

[V]

< 250 AC/DC

Kondisi pengoperasian

Suhu sekitar

[°C]

-20...80

Perlindungan

IP 68

Data teknis

Berat

[g]

22.68

Ulir pemasangan

M16 x 1,5

Material mur

aluminium, dianodisasi

Keterangan

Jumlah paket

1 buah

Koneksi listrik

Kabel: 0.3 m, PVC; 3 x 0.34 mm² / AWG 22

Koneksi listrik - soket

Konektor: 1 x 1/2", lurus; pengkodean: C; Penguncian: aluminium, dianodisasi; Kontak: dilapisi emas



E18253

Soket adaptor

RSTGA030ALS00.3-03



Koneksi

