

E18317



Kabel koneksi

VDOGH040MKS0005E04STGH040MKS



Aplikasi

Fitur khusus	Bebas dari silikon; Bebas halogen; Kontak berlapis emas
Bebas dari silikon	ya

Data kelistrikan

Tegangan pengoperasian	[V]	< 250 AC / < 300 DC
Total beban arus maks.	[A]	3

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...85
Perlindungan		IP 68

Data teknis

Berat	[g]	204.116
Material		PVC
Material bodi detakan		PVC
Material mur		seng, dilapisi epoksi

Keterangan

Jumlah paket	1 buah
--------------	--------

Kabel koneksi

VDOGH040MKS0005E04STGH040MKS

Koneksi listrik - colokan

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: PVC; Penguncian: seng, dilapisi epoksi; Kontak: dilapisi emas; Torsi pengencangan: 0.7...0.9 Nm



Koneksi listrik

Kabel: 0.3 m, PVC, Bebas halogen, kuning, Ø 4.7 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Koneksi



Koneksi listrik - soket

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: PVC; Penguncian: seng, dilapisi epoksi; Kontak: dilapisi emas; Torsi pengencangan: 0.7...0.9 Nm

