


Sensor sinar tembus fiber optik

FE-50-V-V-M5/16



Aplikasi

Prinsip fungsi

Sensor sinar tembus

Zona pendeteksian

Jangkauan dengan tipe
amplifier fiber optik

OBF; ODF; OMF

OBF

Jangkauan fiber optik

[mm]

1000

ODF

Jangkauan fiber optik

[mm]

4

OMF

Jangkauan fiber optik

[mm]

800

Kondisi pengoperasian

Suhu sekitar

[°C]

-58...315

Data teknis

Berat

[g]

197

Versi kepala pendeteksian

lurus

Panjang total

[mm]

900

Radius pembengkokan min.

[mm]

19

Susunan fiber



Material fiber

kaca



Sensor sinar tembus fiber optik

FE-50-V-V-M5/16

Material kepala fiber	baja tahan karat (1.4305/303)
Material selubung fiber	baja tahan karat (1.4305/303)
Aksesori	
Item dikirim	mur segi enam: 4 x M8
	ring penjepit: 2
	O-ring: 2
Keterangan	
Jumlah paket	1 buah