




Sensor refleksi difus fiber optik

FT-50-V-V-M5/16/R



Aplikasi

Prinsip fungsi

Sensor refleksi difus

Zona pendeteksian

Jangkauan dengan tipe
amplifier fiber optik

OBF; ODF; OMF

OBF

Jangkauan fiber optik

[mm]

150

ODF

Jangkauan fiber optik

[mm]

1

OMF

Jangkauan fiber optik

[mm]

175

Kondisi pengoperasian

Suhu sekitar

[°C]

-58...315

Data teknis

Berat

[g]

127.5

Versi kepala pendeteksian

bersiku

Panjang total

[mm]

900

Radius pembengkokan min.

[mm]

19

Susunan fiber

①

Material fiber

kaca



Sensor refleksi difus fiber optik

FT-50-V-V-M5/16/R

Material kepala fiber	baja tahan karat (1.4305/303)
Material selubung fiber	baja tahan karat (1.4305/303)
Aksesori	
Item dikirim	mur segi enam: 2 x M8
	ring penjepit: 2
	O-ring: 2
Keterangan	
Jumlah paket	1 buah