



Sensor sinar tembus fiber optik

FE-50-V-V-E2,3

Produk tidak tersedia - entri arsip

No scale drawing available

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Zona pendeteksian

Jangkauan dengan tipe amplifier fiber optik	OBF
---	-----

OBF

Jangkauan fiber optik [mm]	110
----------------------------	-----

Kondisi pengoperasian

Suhu sekitar [°C]	-58...315
-------------------	-----------

Data teknis

Versi kepala pendeteksian	lurus
Diameter kepala pendeteksian [mm]	8
Panjang total [mm]	900
Radius pembengkokan min. [mm]	19
Material fiber	kaca
Material kepala fiber	baja tahan karat (1.4305/303)
Material selubung fiber	baja tahan karat (1.4305/303)

Keterangan

Jumlah paket	1 buah
--------------	--------