

Sensor refleksi difus fiber optik

FT-00-V-V-M6

Produk tidak tersedia - entri arsip



Aplikasi

Prinsip fungsi

Sensor refleksi difus

Zona pendeteksian

Jangkauan dengan tipe
amplifier fiber optik

OKF; OUF

OKF

Jangkauan fiber optik

[mm]

40

OUF

Jangkauan fiber optik

[mm]

40

Kondisi pengoperasian

Suhu sekitar

[°C]

-40...290

Data teknis

Versi kepala pendeteksian

lurus

Ulir kepala pendeteksian

M6

Panjang kepala pendeteksian [mm]

35

Panjang total

[mm]

600

Radius pembengkokan min.

[mm]

20

Susunan fiber



Material

Adaptor: ABS

**Sensor refleksi difus fiber optik**

FT-00-V-V-M6

Material fiber	kaca
Material kepala fiber	baja tahan karat (1.4305/303)
Material selubung fiber	baja tahan karat (1.4305/303)
Keterangan	
Jumlah paket	1 buah