

Sensor sinar tembus fiber optik

FE-11-EPA-M3/F217X0,06/2M



Aplikasi

Prinsip fungsi

Sensor sinar tembus

Aplikasi

Radius pembengkokan kecil

Zona pendeteksian

Jangkauan dengan tipe
amplifier fiber optik

OB50; OBF; OCF; OO50

OB50

Jangkauan fiber optik

[mm]

50

OBF

Jangkauan fiber optik

[mm]

56

OCF (High Power)

Jangkauan fiber optik

[mm]

560

OO50

Jangkauan fiber optik

[mm]

120

Kondisi pengoperasian

Suhu sekitar

[°C]

-40...60

Data teknis

Berat

[g]

33

Versi kepala pendeteksian

lurus

Ulir kepala pendeteksian

M3

E21103



Sensor sinar tembus fiber optik

FE-11-EPA-M3/F217X0,06/2M

Panjang total	[mm]	2000
Radius pembengkokan min.	[mm]	3
Susunan fiber		●
Diameter core	[mm]	0.5
Diameter fiber	[mm]	217 x 0.06
Diameter eksternal	[mm]	1
Material fiber		PMMA
Material kepala fiber		aluminium
Material selubung fiber		PE

Aksesori	
Item dikirim	mur segi enam: 4 x M3
	washer pengunci bergerigi: 4
	Adaptor: OBF
	Adaptor: OOF
Aksesori (opsional)	Pemotong untuk fiber optik:, E20600

Keterangan	
Jumlah paket	1 buah