


Kabel koneksi dengan colokan

ASTGH030MSS0005B03

Produk tidak tersedia - entri arsip



Data kelistrikan

Tegangan pengoperasian	[V]	10...30 DC
------------------------	-----	------------

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...90
--------------	------	----------

Perlindungan		IP 67
--------------	--	-------

Data teknis

Material	TPU
----------	-----

Material bodi detakan	TPU
-----------------------	-----

Material mur	kuningan, berlapis nikel
--------------	--------------------------

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 5 m, PUR; 3 x 0.25 mm²

Koneksi listrik - colokan

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



E70002



Kabel koneksi dengan colokan

ASTGH030MSS0005B03

Koneksi



BK =	Warna core :
BN =	hitam
BU =	coklat
	biru