



Kabel koneksi

VSTAH040MSS0020A04DOAH040MSS

Produk tidak tersedia - entri arsip



Data kelistrikan

Tegangan pengoperasian	[V]	10...30 DC
------------------------	-----	------------

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67

Data teknis

Material	TPU
Material bodi detakan	TPU
Material mur	kuningan, berlapis nikel

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik - colokan

Konektor: 1 x M12, bersiku; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



E70059



Kabel koneksi

VSTAH040MSS0020A04DOAH040MSS

Koneksi listrik

Kabel: 20 m, PUR / PVC, oranye, Ø 5 mm; 4 x 0.25 mm² (32 x Ø 0.1 mm)

Koneksi



Koneksi listrik - soket

Konektor: 1 x M12, bersiku; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel

