




Kabel jumper dengan soket katup

VVDAA041--S0001A03STGH030MSS

Produk tidak tersedia - entri arsip



Data kelistrikan

Tegangan pengoperasian	[V]	< 24 AC/DC
Pelindung tegangan berlebih		ya; (VDR)

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67

Data teknis

Dimensi	[mm]	15 x 15 x 46.5
Material		TPU
Material bodi detakan		TPU
Material mur		kuningan, berlapis nikel

Elemen display/pengoperasian

Display	operasi	1 x LED, kuning
---------	---------	-----------------

Aksesori

Item dikirim	sekrup
	panel untuk pelabelan

Keterangan

Jumlah paket	1 buah
--------------	--------

Kabel jumper dengan soket katup

VVDAA041--S0001A03STGH030MSS

Koneksi listrik - colokan

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



Koneksi listrik

Kabel: 1 m, PUR / PVC; 3 x 0.5 mm²

Koneksi



Koneksi listrik - soket

Konektor: 1 x katup tipe A DIN, bersiku; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel

