

# E70080



## Kabel jumper dengan soket katup

VVDAA041--S0005A03STGH030MSS

Produk tidak tersedia - entri arsip



### Data kelistrikan

|                             |     |            |
|-----------------------------|-----|------------|
| Tegangan pengoperasian      | [V] | < 24 AC/DC |
| Pelindung tegangan berlebih |     | ya; (VDR)  |

### Kondisi pengoperasian

|              |      |          |
|--------------|------|----------|
| Suhu sekitar | [°C] | -25...90 |
| Perlindungan |      | IP 67    |

### Data teknis

|                       |      |                          |
|-----------------------|------|--------------------------|
| Dimensi               | [mm] | 15 x 15 x 46.5           |
| Material              |      | TPU                      |
| Material bodi detakan |      | TPU                      |
| Material mur          |      | kuningan, berlapis nikel |

### Elemen display/pengoperasian

|         |         |                 |
|---------|---------|-----------------|
| Display | operasi | 1 x LED, kuning |
|---------|---------|-----------------|

### Aksesori

|              |                       |
|--------------|-----------------------|
| Item dikirim | sekrup                |
|              | panel untuk pelabelan |

### Keterangan

|              |        |
|--------------|--------|
| Jumlah paket | 1 buah |
|--------------|--------|

## Kabel jumper dengan soket katup

VVDAA041--S0005A03STGH030MSS

### Koneksi listrik - colokan

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



### Koneksi listrik

Kabel: 5 m, PUR / PVC; 3 x 0.5 mm<sup>2</sup>

### Koneksi



### Koneksi listrik - soket

Konektor: 1 x katup tipe A DIN, bersiku; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel

