




Kabel jumper dengan soket katup

VVDAB031--S01,5A03STGH030MSS

Produk tidak tersedia - entri arsip



Data kelistrikan

Tegangan pengoperasian [V]	< 24 AC/DC
Pelindung tegangan berlebih	ya; (VDR)

Kondisi pengoperasian

Suhu sekitar [°C]	-25...90
Perlindungan	IP 67

Data teknis

Dimensi [mm]	15 x 15 x 46,5
Material	TPU
Material bodi detakan	TPU
Material mur	kuningan, berlapis nikel

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Aksesori

Item dikirim	sekrup
	panel untuk pelabelan

Keterangan

Jumlah paket	1 buah
--------------	--------

Kabel jumper dengan soket katup

VVDAB031--S01,5A03STGH030MSS

Koneksi listrik - colokan


Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



Koneksi listrik

Kabel: 1.5 m, PUR / PVC; 3 x 0.5 mm²

Koneksi



Koneksi listrik - soket

Konektor: 1 x katup tipe B DIN, bersiku; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel

