


E70138



Kabel koneksi

VDOAH040MSS0002A03STGH030MSS

Produk tidak tersedia - entri arsip



Data kelistrikan		
Tegangan pengoperasian	[V]	< 250 AC / < 300 DC
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67
Data teknis		
Material		TPU
Material bodi detakan		TPU
Material mur		kuningan, berlapis nikel
Keterangan		
Jumlah paket		1 buah

Koneksi listrik - colokan

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



E70138




Kabel koneksi

VDOAH040MSS0002A03STGH030MSS

Koneksi listrik

Kabel: 2 m, PUR / PVC; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Koneksi



Koneksi listrik - soket

Konektor: 1 x M12, bersiku; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel

