




Tag RFID

ID-TAG/8.3X3.6/06



lubang pemasangan: Ø 8.0 x 3.7 mm



Aplikasi		
Suhu pengoperasian (aktif)	[°C]	-40...85
Suhu puncak (pasif)	[°C]	90
Data kelistrikan		
Frekuensi pengoperasian	[MHz]	13,56
Ukuran memori	[bit]	896
Tipe memori		EEPROM
Tipe chip		ICODE SLIX
Jumlah blok		28
Ukuran blok	[Byte]	4
Nomor Identifikasi Unik (UID)	[Byte]	8
Standar RFID		ISO 15693
Siklus pembacaan maks.		tidak terbatas
Siklus penulisan maks.		100000
Kondisi pengoperasian		
Suhu sekitar	[°C]	-40...85
Suhu penyimpanan	[°C]	-40...90
Perlindungan		IP 68
Pengujian/persetujuan		
Persetujuan radio		ISO 15693
Data teknis		
Berat	[g]	3.75
Tipe pemasangan		Casing yang dipasang dengan ditekan; Pemasangan pada logam; Pemasangan pada non-logam
Dimensi	[mm]	Ø 8.3 / L = 3.6
Material		casing: PPA GF30; resin epoksi
Keterangan		
Jumlah paket		10 buah