

EVC11A



Kabel koneksi

VDOAH040VAT0001H04STAH040VAT



Aplikasi	
Fitur khusus	Bebas halogen; Kontak berlapis emas
Kompatibel dengan cat	ya
Data kelistrikan	
Tegangan pengoperasian [V]	< 60 AC/DC
Kelas perlindungan	II
Total beban arus maks. [A]	2
Kondisi pengoperasian	
Suhu sekitar [°C]	-20...60
Perlindungan	IP 67; (jika digunakan di luar area berbahaya: IP 68 / IP 69K)
Pengujian/persetujuan	
Persetujuan	BVS 08 ATEX E 109 U; IECEx BVS 08.0041 U
Tanda ATEX	Ex II 3G Ex ec IIC Gc; II 2D Ex tb IIIC Db IP65/IP67
Data teknis	
Berat [g]	84.1
Dimensi [mm]	31 x 15.5 x 36.5
Material	casing: TPU oranye; Segel: FKM
Material mur	baja tahan karat (1.4404 / 316L)
Keterangan	
Jumlah paket	1 buah



Kabel koneksi

VDOAH040VAT0001H04STAH040VAT

Koneksi listrik - colokan

Konektor: 1 x M12, bersiku; pengkodean: A; Penguncian: baja tahan karat (1.4404 / 316L); Kontak: dilapisi emas; Torsi pengencangan: 1.2...1.5 Nm



Koneksi listrik

Kabel: 1 m, PUR, Bebas halogen, hitam, Ø 4.9 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Koneksi



Koneksi listrik - soket

Konektor: 1 x M12, bersiku; pengkodean: A; Penguncian: baja tahan karat (1.4404 / 316L); Kontak: dilapisi emas; Torsi pengencangan: 1.2...1.5 Nm

