

Sensor induktif

IB-3020-BPKG/55V/15M

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	20
Casing	berbentuk silinder
Dimensi [mm]	Ø 34 / L = 82

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Konsumsi arus [mA]	5; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	60
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian


Jangkauan pendeteksian [mm]	20
Jangkauan pendeteksian real Sr	20 ± 10 %
Jarak pengoperasian [mm]	0...16.2



Sensor induktif

IB-3020-BPKG/55V/15M

Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis [X01]		1...15
Deviasi titik peralihan [X01]		-10...10
Kondisi pengoperasian		
Suhu sekitar [°C]		-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing		berbentuk silinder
Pemasangan		non-flush mountable
Dimensi [mm]		Ø 34 / L = 82
Material		PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		Klem pemasangan: 1
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 15 m, PVC; 3 x 0.5 mm ²		
Koneksi		



Warna core :

BN = coklat

BU = biru

BK = hitam