

IDC2040-ARKG/UP/0,80M/PUR/US

Technical drawing of the LED light fixture showing front, side, and detail views with dimensions.

Front View Dimensions:

- Overall width: 92
- Overall height: 80
- Mounting hole spacing (center-to-center): 65
- Distance from top edge to mounting holes: 40
- Distance from left edge to mounting holes: 9,3
- Distance from bottom edge to mounting holes: 7,5
- Distance from right edge to mounting holes: 5,5
- Distance from left edge to mounting holes: 5,5
- Distance from left edge to mounting holes: 9,3

Side View Dimensions:

- Overall width: 40
- Distance from top edge to mounting holes: 20
- LED indicator location: LED

Detail View Dimensions:

- Overall width: 42
- Thread: M12 x 1



Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	40
Casing	persegi panjang
Dimensi [mm]	92 x 80 x 40

Tegangan pengoperasian	[V]	10...55 DC
Kelas perlindungan		II
Pelindung polaritas terbalik		ya

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	4.6
Arus beban minimal [mA]	4
Kebocoran arus maks. [mA]	0.6
Peringkat arus permanen dari output peralihan DC [mA]	400
Frekuensi peralihan DC [Hz]	90
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Sensor induktif

IDC2040-ARKG/UP/0,80M/PUR/US

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	40
Jangkauan pendeteksian real Sr	[mm]	40 ± 10 %
Jarak pengoperasian	[mm]	0...32.4
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis	[X01]	3...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...70
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing		persegi panjang
Pemasangan		non-flush mountable
Dimensi	[mm]	92 x 80 x 40
Material		PPE; kuningan berlapis nikel
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		colokan penyegel: 1
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 0.8 m, PUR		
Koneksi listrik - colokan		
Konektor: 1 x M12; pengkodean: A		
		



Sensor induktif

IDC2040-ARKG/UP/0,80M/PUR/US

Koneksi

