


IF7100



Sensor induktif

IFK3002-BPKG/US-100



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	2
Casing	tipe berulir
Dimensi [mm]	M12 x 1 / L = 60

Aplikasi

Fitur khusus	Kontak berlapis emas
--------------	----------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	< 10
Kelas perlindungan	III
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	800
Pelindung hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	2
Jangkauan pendeteksian real Sr	$2 \pm 10 \%$
Jarak pengoperasian [mm]	0...1.62

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3
Histeresis [X01]	3...15
Deviasi titik peralihan [X01]	-10...10

IF7100



Sensor induktif

IFK3002-BPKG/US-100

Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...70
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF dipancarkan	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF dihantarkan	3 V
	EN 55011	kelas B
MTTF	[ANN]	1134
Termasuk software yang disematkan		tidak
Persetujuan UL	Ta	-25...70 °C
	Tipe penutup	Type 1
	suplai tegangan	Limited Voltage/Current
	Persetujuan UL no.	A001
	Nomor file UL	E174191
Data teknis		
Berat	[g]	30
Casing		tipe berulir
Pemasangan		flush mountable
Dimensi	[mm]	M12 x 1 / L = 60
Penamaan ulir		M12 x 1
Material		casing: kuningan dilapisi perunggu putih; permukaan pendeteksian: PBT oranye; Jendela LED: PEI; mur pengunci: kuningan dilapisi perunggu putih
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah
Koneksi listrik - colokan		
Konektor: 1 x M12; pengkodean: A; Kontak: dilapisi emas		

IF7100



Sensor induktif

IFK3002-BPKG/US-100

Koneksi

