


IIA2015-BBOA/20m






Sensor induktif

IIA2015-BBOA/20m

Jangkauan pendeteksian real [mm] Sr	15 ± 10 %
Jarak pengoperasian [mm]	0...12.1
Akurasi/deviasi	
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis [X01]	1...15
Deviasi titik peralihan [X01]	-10...10
Kondisi pengoperasian	
Suhu sekitar [°C]	-25...80
Perlindungan	IP 67
Pengujian/persetujuan	
EME	EN 60947-5-2
	EN 55011 kelas B
MTTF [ANN]	607
Data teknis	
Casing	tipe berulir
Pemasangan	non-flush mountable
Dimensi [mm]	M30 x 1.5 / L = 81
Penamaan ulir	M30 x 1.5
Material	kuningan berlapis nikel; permukaan pendeteksian: PBT
Koneksi listrik	
Perlindungan yang diperlukan	sekring miniatur sesuai IEC60127-2 lembar 1; ≤ 2 A; cepat
Aksesori	
Item dikirim	mur pengunci: 2
Keterangan	
Keterangan	Rekomendasi: Periksa keamanan fungsi unit setelah hubung singkat.
Jumlah paket	1 buah

Sensor induktif

IIA2015-BBOA/20m

Koneksi listrikKabel: 20 m, PVC; 2 x 0.5 mm²**Koneksi**

Catatan sekring miniatur sesuai IEC60127-2 lembar 1 ≤ 2 A cepat

Warna core :

BN =

coklat

BU =

biru