




Sensor ganda induktif untuk aktuatur katup

IND3004DBPKG/10M



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	2 x biasanya terbuka
Jangkauan pendeteksian [mm]	4
Casing	persegi panjang
Dimensi [mm]	40 x 26 x 26

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	2 x biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	1300
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	4
Jangkauan pendeteksian real Sr	$4 \pm 10\%$
Jarak pengoperasian [mm]	0...3.25

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3
Histeresis [X01]	1...15



Sensor ganda induktif untuk aktuatur katup

IND3004DBPKG/10M

Deviasi titik peralihan	[X01]	-10...10
-------------------------	-------	----------

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF	[ANN]	1064

Data teknis

Berat	[g]	446
Casing		persegi panjang
Pemasangan		non-flush mountable
Dimensi	[mm]	40 x 26 x 26
Material		PBT; PC

Elemen display/pengoperasian

Display	status peralihan	2 x LED, kuning
---------	------------------	-----------------


Keterangan

Jumlah paket		1 buah
--------------	--	--------

Koneksi listrik

Kabel: 10 m, PVC; 4 x 0.34 mm²

Koneksi



	Warna core :
BN =	coklat
BU =	biru
BK =	hitam
WH =	putih