


Sensor aliran untuk koneksi ke satu unit evaluasi

STM12ABB/US-100-H

Produk tidak tersedia - entri arsip



Karakteristik produk

Koneksi proses	M12 x 1
----------------	---------

Aplikasi

Aplikasi	rentang suhu tinggi
Media	Cairan; Gas
Suhu media [°C]	-25...80
Peringkat tekanan [bar]	30

Cairan

Aplikasi	rentang suhu tinggi
Suhu media [°C]	-25...80

Gas

Suhu media [°C]	-25...80
-----------------	----------

Data kelistrikan

Koneksi ke monitor kontrol	VS 0100
----------------------------	---------

Rentang pengukuran/pengaturan

Cairan

Rentang pengaturan [cm/s]	3...300
Sensitivitas terbesar [cm/s]	3...60

Gas

Rentang pengaturan [cm/s]	5...1500
---------------------------	----------

Akurasi/deviasi

Gradien suhu [K/min]	15
----------------------	----

Waktu respons

Waktu respons [s]	1...10
-------------------	--------

Cairan

Waktu respons [s]	1...10
-------------------	--------

Gas

Waktu respons [s]	1...10
-------------------	--------

Kondisi pengoperasian

Perlindungan	IP 67
--------------	-------

ST1204



Sensor aliran untuk koneksi ke satu unit evaluasi

STM12ABB/US-100-H

Data teknis

Casing		tipe berulir
Dimensi	[mm]	M12 x 1
Penamaan ulir		M12 x 1
Material		baja tahan karat (1.4571 / 316Ti)
Koneksi proses		M12 x 1

Keterangan


Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Konektor: 1 x M12; pengkodean: A; Panjang kabel maksimal: 100 m



Koneksi



BK = Warna core :
BN = hitam
BU = coklat
WH = biru
 putih