




Sensor aliran untuk koneksi ke satu unit evaluasi

STR14AAC/US-100-H

Produk tidak tersedia - entri arsip



Karakteristik produk

Koneksi proses	G 1/4 ulir eksternal
----------------	----------------------

Aplikasi

Media	Cairan; media agresif
-------	-----------------------

Suhu media	[°C]	-25...80
------------	------	----------

Peringkat tekanan	[bar]	5
-------------------	-------	---

Cairan

Suhu media	[°C]	-25...80
------------	------	----------

Data kelistrikan

Koneksi ke monitor kontrol	VS 0100
----------------------------	---------

Rentang pengukuran/pengaturan

Cairan

Rentang pengaturan	[cm/s]	3...300
--------------------	--------	---------

Sensitivitas terbesar	[cm/s]	3...60
-----------------------	--------	--------

Akurasi/deviasi

Gradien suhu	[K/min]	7
--------------	---------	---

Waktu respons

Waktu respons	[s]	2...20
---------------	-----	--------

Cairan

Waktu respons	[s]	2...20
---------------	-----	--------

Kondisi pengoperasian

Perlindungan	IP 67
--------------	-------

Data teknis

Casing	tipe berulir
--------	--------------

ST2404



Sensor aliran untuk koneksi ke satu unit evaluasi

STR14AAC/US-100-H


Material	PTFE
Koneksi proses	G 1/4 ulir eksternal
Keterangan	
Jumlah paket	1 buah

Koneksi listrik

Konektor: 1 x M12; pengkodean: A; Panjang kabel maksimal: 100 m



Koneksi



BK = Warna core :
BN = hitam
BU = coklat
WH = biru
 putih