


Produk tidak tersedia - entri arsip

**Karakteristik produk**

Koneksi proses	G 1/2 ulir eksternal
----------------	----------------------

Aplikasi

Aplikasi	Eks zona 1
Suhu media [°C]	-25...80
Peringkat tekanan [bar]	30

Cairan

Aplikasi	Eks zona 1
Suhu media [°C]	-25...80

Gas

Suhu media [°C]	-25...80
-----------------	----------

Data kelistrikan

Koneksi ke monitor kontrol	VS 0100 Ex
----------------------------	------------

Rentang pengukuran/pengaturan**Cairan**

Rentang pengaturan [cm/s]	3...300
Sensitivitas terbesar [cm/s]	3...60

Gas

Rentang pengaturan [cm/s]	200...2000
Sensitivitas terbesar [cm/s]	100...800

Akurasi/deviasi

Gradien suhu [K/min]	15
----------------------	----

Waktu respons

Waktu respons [s]	1...10
-------------------	--------



Sensor aliran untuk koneksi ke satu unit evaluasi

STR12ABBE1

Cairan		
Waktu respons	[s]	1...10
Gas		
Waktu respons	[s]	1...10
Kondisi pengoperasian		
Perlindungan		IP 67
Data teknis		
Casing		tipe berulir
Material		baja tahan karat (1.4571 / 316Ti)
Koneksi proses		G 1/2 ulir eksternal
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 2 m, Silflex-PUR; Panjang kabel maksimal: 100 m; 4 x 0.34 mm ²		
Koneksi		



BN =
 GN =
 WH =
 YE =

Warna core :
 coklat
 hijau
 putih
 kuning