



No scale drawing available



Aplikasi	
Aplikasi	Master AS-i untuk platform PLC ControlLogix
Data kelistrikan	
Tegangan pengoperasian [V]	30 DC; (AS-i)
Konsumsi arus [mA]	5,1 V DC: 390 mA; 24 V DC: 150 mA; AS-i 1: 70 mA; AS-i 2: 70 mA
Jumlah master AS-i	2
Interface	
Interface komunikasi	RS232
RS232	
Jumlah interface R232	1
Laju transmisi	9600...115200 Baud
Tipe konektor	RJ11
Tipe penggunaan	pemrograman
Kondisi pengoperasian	
Suhu sekitar [°C]	0...55
Suhu penyimpanan [°C]	-25...85
Perlindungan	IP 20
Klasifikasi AS-i	
Versi AS-i	3.0
Data teknis	
Berat [g]	305
Elemen display/pengoperasian	
Display	Display batang LED
Keterangan	
Keterangan	Konfigurasi ditangani melalui software RSLogix Allen-Bradleys.

U71005



Gateway AS-Interface ControlLogix

AS-i MASTER (A-B)

Jumlah paket

1 buah