



## Switching amplifier

N600/230VAC/0,08A

Article no longer available - archive entry

Alternative articles: DN0200

When selecting an alternative article and accessories please note that technical data may differ!

# No scale drawing available



## Product characteristics

Housing	housing for DIN rail mounting
---------	-------------------------------

## Application

Application	Power supply and signal evaluation
-------------	------------------------------------

## Electrical data

Nominal voltage AC	[V]	< 230
Nominal voltage tolerance	[%]	10
Nominal voltage tolerance 2	[%]	10
Nominal frequency AC	[Hz]	47...63
Auxiliary energy for sensors DC	[V]	24; ( $\pm 5\%$ , $\leq 40\text{ mA}$ )

## Outputs

Contact rating	4 A / 625 VA / 250 V AC
----------------	-------------------------

## Operating conditions

Ambient temperature	[°C]	0...50
Protection		IP 40
Protection rating terminals		IP 20

## Mechanical data

Housing	housing for DIN rail mounting
Materials	plastics

# DN0202



## Switching amplifier

N600/230VAC/0,08A

### Displays / operating elements

Display	switching status	LED, green
	operation	1 x LED, green

### Electrical connection

terminals: ...4 mm<sup>2</sup>

### Connection