


Fibre optic diffuse reflection sensor

FT-00-P-A-M6/0,29M



Application

Function principle	Diffuse reflection sensor
Application	For use in industrial environments

Detection zone

Range with fibre optic amplifier type	OKF; OUF; OOF
---------------------------------------	---------------

OKF

Range fibre optics [mm]	40
-------------------------	----

OOF

Range fibre optics [mm]	200
-------------------------	-----

OUF

Range fibre optics [mm]	40
-------------------------	----

Operating conditions

Ambient temperature [°C]	-20...80
--------------------------	----------

Mechanical data

Weight [g]	36.5
Version of sensing head	straight
Sensing head thread	M6
Sensing head length [mm]	25
Total length [mm]	290; (+20 mm)

E20423



Fibre optic diffuse reflection sensor

FT-00-P-A-M6/0,29M

Min. bending radius	[mm]	20
Fibre arrangement		
Fibre material		glass
Fibre head material		aluminium
Fibre sheath material		PVC
Accessories		
Items supplied		hexagon nuts: 2 x M6, stainless steel
		tooth lock washers: 2
		knurled nut: 1 x M11
Remarks		
Pack quantity		1 pcs.