

OIP-FBOW

[illegible]

Housing	threaded type
---------	---------------

Special feature	polarisation filter
-----------------	---------------------

Electrical data

Frequency AC	[Hz]	47...63
--------------	------	---------

Outputs

Output function	light-on/dark-on mode; (parameterisable)
-----------------	--

Detection zone

Range	[m]	< 2; (Prismatic reflector Ø 80 E20005)
-------	-----	--

Operating conditions

Ambient temperature	[°C]	-25...60
---------------------	------	----------



Retro-reflective sensor

OIP-FBOW

Protection		IP 65	
Tests / approvals			
EMC		EN 60947-5-2	
Mechanical data			
Housing		threaded type	
Dimensions [mm]		M30 x 1.5 / L = 125	
Thread designation		M30 x 1.5	
Materials		PBT; PPO modified	
Lens material		PMMA	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Accessories			
Items supplied		lock nuts: 2	
		screwdrivers	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
terminals: ...1.5 mm²			
Connection			

