


AC508A



AS-Interface ClassicLine module with quick mounting technology

ClassicLine 4DO II 3D



Electrical data	
Operating voltage [V]	26.5...31.6 DC
Max. current consumption from AS-i [mA]	50
Max. current load total [A]	2
Integrated watchdog	yes
Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 4
Outputs	
Number of digital outputs	4
Circuit	PNP
Voltage range DC [V]	15...30; (to PELV; via flat cable)
Max. current load per output [mA]	1000; (utilisation category DC-13 (control of electromagnets): 20 W (IEC 60947-5-1))
Short-circuit proof	yes
Electrically separated	yes
Operating conditions	
Ambient temperature [°C]	-10...50
Protection	IP 50
Tests / approvals	
ATEX marking	II 3D Ex tc IIIB T80°C Dc X IP50
EMC	EN 50295 IEC 61000-6-2
MTTF [years]	211

AC508A



AS-Interface ClassicLine module with quick mounting technology

ClassicLine 4DO II 3D

AS-i classification					
AS-i version	2.11 + 3.0				
AS-i addressing	addressing socket				
Extended addressing mode possible	no				
AS-i profile	S-8.0.E				
AS-i I/O configuration [hex]	8				
AS-i ID code [hex]	0.E				
AS-i certificate pending	yes				
Assignment of the data bits	data bit	D0	D1	D2	D3
	Output	1	2	3	4
	socket	O-1	O-2	O-3	O-4
	pin	4	4	4	4

Mechanical data	
Weight [g]	228.5
Type of mounting	AS-i flat cables directly connectable
Materials	PA; piercing contacts: CuSn6 nickel-plated and tin-plated

Displays / operating elements		
Display	operation	LED, green
	errors	LED, red
	function	LED, yellow

Accessories	
Accessories (supplied)	lower part
Accessories (optional)	Protective cap: M12, E73004
	Impact protection housing, E7000A

Remarks	
Remarks	Mechanical protection has to be implemented. Otherwise the unit must be installed together with the impact protection housing (E7000A).
Pack quantity	1 pcs.

Electrical connection	
quick mounting technology for AS-i flat cable: ; three orientations possible	
	Outputs
1	not used
2	not used
3	external voltage AUX -
4	switching output +
5	not used
Connector: M12	

AC508A



AS-Interface ClassicLine module with quick mounting technology

ClassicLine 4DO II 3D

