



## Switching amplifier

N600/110VAC/0,1A

Article no longer available - archive entry

Alternative articles: DN0210

When selecting an alternative article and accessories please note that technical data may differ!

# No scale drawing available



## Product characteristics

Housing	housing for DIN rail mounting
---------	-------------------------------

## Application

Application	Power supply and signal evaluation
-------------	------------------------------------

## Electrical data

Nominal voltage AC	[V]	< 110
Nominal voltage tolerance	[%]	10
Nominal voltage tolerance 2	[%]	10
Nominal frequency AC	[Hz]	47...63
Auxiliary energy for sensors DC	[V]	24; ( $\pm 5\%$ , $\leq 100\text{ mA}$ )

## Inputs / outputs

Number of inputs and outputs	Number of relay outputs: 1
------------------------------	----------------------------

## Outputs

Number of relay outputs	1
Contact rating	8 A / 1250 VA / 250 V AC

## Operating conditions

Ambient temperature	[°C]	0...50
Protection		IP 40
Protection rating terminals		IP 20

# DN0012



## Switching amplifier

N600/110VAC/0,1A

Mechanical data		
Weight	[g]	430.4
Housing	housing for DIN rail mounting	
Materials	plastics	

Displays / operating elements		
Display	switching status	LED, red
	operation	1 x LED, green

Electrical connection	
terminals: ...4 mm <sup>2</sup>	
Connection	

