


Fibre optic diffuse reflection sensor

FT-11-EPV-E3/F2X0,5/2M



Application

Function principle	Diffuse reflection sensor
Application	Small bending radius

Detection zone

Range with fibre optic amplifier type	OB50; OBF; OCF; OO50
---------------------------------------	----------------------

OB50

Range fibre optics [mm]	20
-------------------------	----

OBF

Range fibre optics [mm]	25
-------------------------	----

OCF (High Power)

Range fibre optics [mm]	170
-------------------------	-----

OO50

Range fibre optics [mm]	60
-------------------------	----

Operating conditions

Ambient temperature [°C]	-40...70
--------------------------	----------

Mechanical data

Weight [g]	39.5
Version of sensing head	straight
Sensing head diameter [mm]	3

E20711



Fibre optic diffuse reflection sensor

FT-11-EPV-E3/F2X0,5/2M

Total length	[mm]	2000
Min. bending radius	[mm]	10
Fibre arrangement		⊙
Core diameter	[mm]	2 x 0.5
Fibre material		PMMA
Fibre head material		stainless steel (303/1.4305)
Fibre sheath material		PE

Accessories

Accessories (optional)	Cutter for fibre optics:, E20600
------------------------	----------------------------------

Remarks

Pack quantity	1 pcs.
---------------	--------