


E20053



Fibre optic diffuse reflection sensor

FT-00-P-V-E1



Application	
Function principle	Diffuse reflection sensor
Detection zone	
Range with fibre optic amplifier type	OKF; OUF; OOF
OKF	
Range fibre optics [mm]	8
OOF	
Range fibre optics [mm]	24
OUF	
Range fibre optics [mm]	8
Operating conditions	
Ambient temperature [°C]	-20...80

E20053



Fibre optic diffuse reflection sensor

FT-00-P-V-E1

Mechanical data	
Weight [g]	37.2
Version of sensing head	straight
Sensing head diameter [mm]	1
Sensing head length [mm]	5
Total length [mm]	600
Min. bending radius [mm]	20
Fibre arrangement	Ⓜ
Materials	Adapter: PPE
Fibre material	glass
Fibre head material	stainless steel (1.4305 / 303)
Fibre sheath material	PVC
Accessories	
Accessories (supplied)	E20107
Remarks	
Pack quantity	1 pcs.