

MKT3000-ANKG/AS



Technical drawing of the LED module showing front and side views with dimensions.

Front View (Top):

- Overall width: 13,5
- Overall height: 13,5
- Mounting hole: M8x1
- Internal width: 10
- Internal height: 1
- Bottom mounting hole: (1)

Side View (Bottom):

- Overall width: 14,3
- Overall height: 26
- Mounting hole: M8x1
- Internal width: 7
- Internal height: 13
- Bottom mounting hole: M 3
- LED location: LED
- Bottom mounting hole: 1,8

CE

ご参照ください。日本の計量法や法規に適合しない単位表示の製品は日本国内では使用できません。— JA-JP — MK5042-00 — 06.03.2003 —

MK5042




Tスロットシリンダセンサ

MKT3000-ANKG/AS

監視範囲		
磁気感度	[mT]	2
ターゲット移動速度	[m/s]	< 5
精度 / 誤差		
ヒステリシス	[mm]	1
繰返し精度	[mm]	0.1
使用環境条件		
使用周囲温度	[°C]	-25～75
保護構造		IP 67
試験 / 認証		
EMC	EN 60947-5-2	
衝撃耐性 / 振動耐性	30 g (11 ms) / 10-55 Hz (1 mm)	
機械的仕様		
検出面	前面、正面、前部、フロント	
円筒形	台形スロットシリンダー	
外形寸法	[mm]	14 x 12 x 26
材質	アルミニウム, 樹脂外装	
ディスプレイ / パーツ		
表示	スイッチング状態	1 x LED, 黄色
備考		
梱包数	1 個	
電気接続 - プラグ		

コネクタ式: 1 x M8, コーディング: A



接続

