


## Flexible coupling for encoders

COUPLING 25-6-8-32-KV

phase-out article



## Mechanical data

Weight	[g]	35.5
Dimensions	[mm]	Ø 25 / L = 32
Materials		aluminium
External diameter D	[mm]	25
Inside diameter 1	[mm]	6
Inside diameter 2	[mm]	8
Length L	[mm]	32
Depth of the clamping hub	[mm]	8
Clamping screw	[mm]	M3
Max. revolution, mechanical [U/min]		6000
Max. axial shaft misalignment [mm]		± 0,5
Max. radial shaft misalignment [mm]		± 0,35
Max. angular displacement [°]		± 4,0

## Remarks

Remarks	The data indicated apply to couplings with the above hub borings at an ambient temperature of 23 °C.  The values of radial, angular and axial displacement are maximum values which must not reach their maximum simultaneously while in operation.
Pack quantity	1 pcs.