




Wirable plug

SSTGK120--LFGSG

Article no longer available - archive entry



Electrical data

Operating voltage	[V]	4.5...30 DC
-------------------	-----	-------------

Operating conditions

Ambient temperature	[°C]	-40...125
Protection		IP 67

Mechanical data

Weight	[g]	53.2
Dimensions	[mm]	26 x 26 x 53
Materials		brass in plastic sheath; PA 6.6 black
Moulded-body material		brass / PA 6.6, in plastic sheath

Remarks


Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

soldering: ...1 mm²

Electrical connection - plug

Connector: 1 x M23, straight; Moulded body: brass / PA 6.6, in plastic sheath



E60141



Wirable plug
SSTGK120--LFKSG

Connection

