

E11585




Connecting cable with plug

ASTGH040VAS0002E04

Article no longer available - archive entry

Alternative articles: EVT073
When selecting an alternative article and accessories please note that technical data may differ!



Application	
Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes
Electrical data	
Operating voltage [V]	< 250 AC / < 300 DC
Operating conditions	
Ambient temperature [°C]	-25...100
Protection	IP 68; IP 69K
Mechanical data	
Dimensions [mm]	15 x 15 x 41.5
Materials	PVC
Moulded-body material	PVC
Material nut	stainless steel (316L/1.4404)
Remarks	
Pack quantity	1 pcs.

E11585



Connecting cable with plug

ASTGH040VAS0002E04

Electrical connection

Cable: 2 m, PVC, orange, Ø 5.3 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: PVC; Locking: stainless steel (316L/1.4404); Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm



Connection

1	BN
2	WH
3	BU
4	BK

	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white