



Adapter socket

RSTGA030ALS00.3-03

No scale drawing available

Application	
Special feature	Gold-plated contacts
Electrical data	
Operating voltage [V]	< 250 AC/DC
Operating conditions	
Ambient temperature [°C]	-20...80
Protection	IP 68
Mechanical data	
Weight [g]	22.68
Mounting thread	M16 x 1,5
Material nut	aluminium, anodised
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Cable: 0.3 m, PVC; 3 x 0.34 mm² / AWG 22	
Electrical connection - socket	
Connector: 1 x 1/2", straight; coding: C; Locking: aluminium, anodised; Contacts: gold-plated	



E18253



Adapter socket

RSTGA030ALS00.3-03

Connection

