


Connection cable

VSTGH030MSS0015A03DOGF030MSS

Article no longer available - archive entry



Electrical data

Operating voltage [V] 10...30 DC

Protection class III

Operating conditions

Ambient temperature [°C] -25...90

Protection IP 67

Mechanical data

Materials TPU

Moulded-body material TPU

Material nut brass, nickel-plated

Remarks

Pack quantity 1 pcs.

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



E70021



Connection cable

VSTGH030MSS0015A03DOGF030MSS

Electrical connection

Cable: 15 m, PUR / PVC; 3 x 0.34 mm²

Connection



Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated

