



Cage clamp

Cage clamps / 6 pcs.



Electrical data

Max. load current	[A]	10; (2,5 mm ²)
-------------------	-----	----------------------------

Operating conditions

Ambient temperature	[°C]	-40...115
---------------------	------	-----------

Mechanical data

Weight	[g]	41.1
Materials		current carrying parts: copper alloy tin-plated; PA
Tightening torque	[Nm]	0.5

Remarks

Pack quantity		6 pcs.
---------------	--	--------

Electrical connection

0.2...2.5 mm²; Abisolierlänge: 9...10 mm