
EVC084

Connecting cable with socket

ADOGH040MSS0025H04



Application		
Special feature		Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC
Protection class		II
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-2590
Note on ambient temperature		cULus:75 °C
Ambient temperature (moving)	[°C]	-2590
Note on ambient temperature (moving)		cULus:75 °C
Storage temperature	[°C]	-2555
Storage humidity	[%]	10100
Other climatic conditions for storage according to stated class		1K22/ DIN 60721-3-1
Protection		IP 65; IP 67; IP 68; IP 69K
Mechanical data		
Weight	[g]	696.1
Dimensions	[mm]	15.5 x 15.5 x 45

EVC084

Connecting cable with socket



ADOGH040MSS0025H04

Materials	housing: TPU orange; Sealing: FKM		
Material nut	brass, nickel-plated		
Drag chain suitability	yes		
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter	
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ²	
	bending cycles	> 5 Mio.	
	torsional strain	± 180 °/m	
Remarks			
Notes	Please see the technical note under "Downloads"		
Pack quantity	1 pcs.		
Electrical connection			
Cable: 25 m, PUR, Halogen-free	e, black, Ø 4.3 mm; 4 x 0.34 mm² (42 x Ø 0.1 r	nm)	
Electrical connection - socke	t		
Connector: 1 x M12, straight; co	oding: A; Locking: brass, nickel-plated; Contact	s: gold-plated; Tightening torque: 0.61.5 Nm	

5 <u>6</u>°°

Connection

<u>_1</u>	BN
ر 2	WH
<u>3</u>	BU
ر 4	BK
<u> </u>	

	Core colours :	
BK =	black	
BK = BN = BU =	brown	
BU =	blue	
WH =	white	

EVC084

Connecting cable with socket

ADOGH040MSS0025H04

Diagrams and graphs



