



Basic license of the VSE OPC UA server

VSE OPC UA SERVER LIC



Application

Application	OPC UA server software for ifm diagnostic electronics type VSE
Device management	Simple detection of devices via network search or IP addressing
User management	assignment of user roles and rights creation of user groups
Licence management	Adding and managing VSE OPC UA server licences continuous licence extension possible

Software / programming

Language	German; English
Data carrier	download
Type of licence	single licence
Licence class	full version



Basic license of the VSE OPC UA server

VSE OPC UA SERVER LIC

System requirements	
CPU type (or better)	X64 or X86
Min. CPU cycle	2,3 GHz
Min. number of CPU cores	4
Min. RAM	8 GB
Min. graphic resolution	1920 x 1080
Required device interface	USB; LAN Adapter - RJ45
Network card	Ethernet 1 Gbit
Network protocol	Ethernet TCP/IP
Operating system	Linux (Debian based) Docker & Docker Compose; Microsoft Windows 11 64-bit; Microsoft Windows 10 64 Bit; Microsoft Windows Server 2019; Microsoft Windows Server 2016; .NET Framework 4.7.2 or higher; (only versions within the Microsoft support period)
Web browser	Google Chrome; Mozilla Firefox; (supported versions: see current release notes)
Additionally required software	VOD001 VSE OPC UA server device licence
Application	
Min. hard disk memory	1 GB
Log files	
Min. hard disk memory	5 GB
Non process data	
Min. hard disk memory	5 GB
Process data	
Min. hard disk memory	64 GB
Mechanical data	
Weight [g]	0.001
Remarks	
Remarks	Note : This product includes software under the OPC Redistributables Agreement of Use of the OPC Foundation in the version valid when the order is placed