


E10616



Connecting cable with socket

ADOAH042ZDS0005A04

Article no longer available - archive entry



Electrical data

Operating voltage [V] 10...30 DC

Outputs

Electrical design PNP

Operating conditions

Ambient temperature [°C] -25...90

Protection IP 67

Mechanical data

Dimensions [mm] 36 x 15 x 26

Materials PUR

Moulded-body material PUR

Material nut diecast zinc, nickel-plated

Remarks

Pack quantity 1 pcs.

E10616



Connecting cable with socket

ADOAH042ZDS0005A04

Electrical connection


Cable: 5 m, PVC, black, Ø 4.5 mm; 4 x 0.34 mm² (182 x Ø 0.05 mm)

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: PUR; Locking: diecast zinc, nickel-plated



Connection



BK =	Core colours :
BN =	black
BU =	brown
WH =	blue
	white